

Eaton QBGFEP2030

Catalog Number: QBGFEP2030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

General specifications

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2030
UPC	Product Length/Depth
786679145173	5.6 in
Product Height	Product Width
0.7 in	2.4 in
Product Weight	Certifications
0.7 lb	UL 943
Catalog Notes	
HACR rated	



Physical Attributes

Circuit breaker type
QBGF

Number of poles
Two-pole

Type
Ground fault circuit breaker

Performance Ratings

Amperage Rating
30 A

Interrupt rating
10 kAIC

Trip Type
Non-Interchangeable

Voltage rating
120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QBGFEP2030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia