

Specifications

Eaton QBGFT1015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications

| | |
|----------------------|-------------------------------|
| PRODUCT NAME | Eaton QB GFCI circuit breaker |
| CATALOG NUMBER | QBGFT1015 |
| UPC | 786680130953 |
| PRODUCT LENGTH/DEPTH | 1 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.5 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL 489 |



Physical Attributes

| | |
|----------------------|------------------------------|
| CIRCUIT BREAKER TYPE | QBGF |
| MOUNTING METHOD | Bolt-on |
| NUMBER OF POLES | Single-pole |
| TYPE | Ground fault circuit breaker |

Performance Ratings

| | |
|------------------|-----------------------|
| AMPERAGE RATING | 15 A |
| INTERRUPT RATING | 10 kAIC |
| TRIP TYPE | Non-Interchangeable |
| TRIP RATING | 5 mA trip sensitivity |

| | |
|------------------|--------------------------------|
| WIRE SIZE | #14-10 AWG Cu #12-10 AWG Al |
|------------------|--------------------------------|

| | |
|-----------------------|-----------|
| VOLTAGE RATING | 120/240 V |
|-----------------------|-----------|

| Miscellaneous | |
|-------------------------|-----------------------|
| SPECIAL FEATURES | 5 mA Trip Sensitivity |

| Resources | |
|--------------------------------------|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBGFT1015 |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications

Eaton QBGFT1015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications

| | |
|----------------------|-------------------------------|
| PRODUCT NAME | Eaton QB GFCI circuit breaker |
| CATALOG NUMBER | QBGFT1015 |
| UPC | 786680130953 |
| PRODUCT LENGTH/DEPTH | 1 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.5 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL 489 |



Physical Attributes

| | |
|----------------------|------------------------------|
| CIRCUIT BREAKER TYPE | QBGF |
| MOUNTING METHOD | Bolt-on |
| NUMBER OF POLES | Single-pole |
| TYPE | Ground fault circuit breaker |

Performance Ratings

| | |
|------------------|-----------------------|
| AMPERAGE RATING | 15 A |
| INTERRUPT RATING | 10 kAIC |
| TRIP TYPE | Non-Interchangeable |
| TRIP RATING | 5 mA trip sensitivity |

| | |
|------------------|--------------------------------|
| WIRE SIZE | #14-10 AWG Cu #12-10 AWG Al |
|------------------|--------------------------------|

| | |
|-----------------------|-----------|
| VOLTAGE RATING | 120/240 V |
|-----------------------|-----------|

| Miscellaneous | |
|-------------------------|-----------------------|
| SPECIAL FEATURES | 5 mA Trip Sensitivity |

| Resources | |
|--------------------------------------|---|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBGFT1015 |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

