Specifications



Eaton QBGFT1030

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,30A,10 kAIC,Singlepole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#10 Cu, #8 Al,QBGF

General specifications	
PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1030
UPC	786680130984
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489



Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
ТҮРЕ	Ground fault circuit breaker

Performance Ratings	
AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity

WIRE	SIZE
------	------

#10 Cu, #8 Al

VOLTAGE RATING

120/240 V

Miscellaneous

SPECIAL FEATURES

5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	QBGFT1030

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House

30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

