

Eaton QBGFT1040

Catalog Number: QBGFT1040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

General specifications



Photo is representative

Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBGFT1040

UPC

786680130991

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

0.5 lb

Warranty

1 year

Certifications

UL 489

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#8 Cu

#8–6 Al

Performance Ratings

Amperage Rating

40 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBGFT1040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia