

Eaton QBGFT2030

Catalog Number: QBGFT2030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFT2030
UPC	Product Length/Depth
786676026734	4.5 in
Product Height	Product Width
2 in	2.75 in
Product Weight	Warranty
0.6 lb	1 year
Certifications	Catalog Notes
UL 489	HACR rated

Physical Attributes

Circuit breaker type
QBGF

Mounting Method
Bolt-on

Number of poles
Two-pole

Type
Ground fault circuit breaker

Wire size
#10 Cu, #8 Al

Performance Ratings

Amperage Rating
30 A

Interrupt rating
10 kAIC

Trip Type
Common trip

Trip rating
5 mA trip sensitivity

Voltage rating
120/240 V

Miscellaneous

Special features
5 mA Trip Sensitivity

Resources

Brochures
[Loadcenters and Circuit Breakers](#)

Specifications and datasheets
[Eaton Specification Sheet - QBGFT2030](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)