

# Specifications

## Eaton QBGFT2040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBGFT2040
<b>UPC</b>	786676026741
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.6 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated



### Physical Attributes

**CIRCUIT BREAKER TYPE** QBGF

### Performance Ratings

**AMPERAGE RATING** 40 A

<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#8 Cu #8-6 Al

<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Common trip
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

### Miscellaneous

<b>SPECIAL FEATURES</b>	5 mA Trip Sensitivity
-------------------------	-----------------------

### Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFT2040</a>
--------------------------------------	---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

