

# Eaton QBHGFT1020

Catalog Number: QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBHGFT1020
<b>UPC</b>	<b>Product Length/Depth</b>
786680131035	5 in
<b>Product Height</b>	<b>Product Width</b>
1 in	3 in
<b>Product Weight</b>	<b>Warranty</b>
0.4 lb	1 year
<b>Certifications</b>	
UL 489	

## Physical Attributes

### Circuit breaker type

QBHGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHGFT1020](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBHGFT1020

Catalog Number: QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

## General specifications



### Product Name

Eaton QB GFCI circuit breaker

### Catalog Number

QBHGFT1020

### UPC

786680131035

### Product Length/Depth

5 in

### Product Height

1 in

### Product Width

3 in

### Product Weight

0.4 lb

### Warranty

1 year

### Certifications

UL 489



Powering Business Worldwide

## Physical Attributes

### Circuit breaker type

QBHGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHGFT1020](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)