

Eaton QBHGFT1020

Catalog Number: QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

General specifications



Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBHGFT1020

UPC

786680131035

Product Length/Depth

5 in

Product Height

1 in

Product Width

3 in

Product Weight

0.4 lb

Warranty

1 year

Certifications

UL 489



Powering Business Worldwide

Physical Attributes

Circuit breaker type
QBHGF

Mounting Method
Bolt-on

Number of poles
Single-pole

Type
Ground fault circuit breaker

Performance Ratings

Amperage Rating
20 A

Interrupt rating
22 kAIC

Trip Type
Non-Interchangeable

Trip rating
5 mA trip sensitivity

Voltage rating
120/240 V

Miscellaneous

Special features
5 mA Trip Sensitivity

Resources

Brochures
[Loadcenters and Circuit Breakers](#)

Specifications and datasheets
[Eaton Specification Sheet - QBHGFT1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)