

Eaton QBHGFT1020

Catalog Number: QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF

General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBHGFT1020
UPC	Product Length/Depth
786680131035	5 in
Product Height	Product Width
1 in	3 in
Product Weight	Warranty
0.4 lb	1 year
Certifications	
UL 489	

Physical Attributes

Circuit breaker type

QBHGF

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHGFT1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)