

# Specifications

## Eaton QBHGFT1020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip Sensitivity, QBHGF



### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBHGFT1020
<b>UPC</b>	786680131035
<b>PRODUCT LENGTH/DEPTH</b>	5 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	0.4 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 489

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHGF
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Ground fault circuit breaker

## Miscellaneous

<b>SPECIAL FEATURES</b>	5 mA Trip Sensitivity
-------------------------	-----------------------

## Performance Ratings

<b>AMPERAGE RATING</b>	20 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBHGFT1020</a>
--------------------------------------	--------------------------------------------------------

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

