

# Eaton QBHGFT2020

Catalog Number: QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBHGFT2020
UPC	Product Length/Depth
786676027823	4.5 in
Product Height	Product Width
2 in	2.75 in
Product Weight	Certifications
0.6 lb	UL 489
Catalog Notes	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBHGF

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHGFT2020](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)