

Specifications

Eaton QBHW1020

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 20A, 22 kAIC, 120/240V



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1020
UPC	786679392058
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	1.2 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Switching duty rated for 120V fluorescent light applications, HACR rated



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

Miscellaneous

QUANTITY	17
-----------------	----

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW1020
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton QBHW1020

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 20A, 22 kAIC, 120/240V



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW1020
UPC	786679392058
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	1.2 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Switching duty rated for 120V fluorescent light applications, HACR rated

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous

QUANTITY	17
-----------------	----

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW1020
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

