

# Eaton QBHW1045

Catalog Number: QBHW1045

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 45A, 22 kAIC, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB thermal magnetic circuit breaker	QBHW1045
	UPC
	786679152461
<b>Product Length/Depth</b>	<b>Product Height</b>
1 in	1 in
<b>Product Width</b>	<b>Product Weight</b>
1 in	1 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed
<b>Catalog Notes</b>	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

45 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

17

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHW1045](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)