

Eaton QBHW2050

Catalog Number: QBHW2050

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 50A, 22 kAIC, 120/240V , Bolt-on

General specifications



Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW2050
	UPC
	786679392805
Product Length/Depth	Product Height
3.8 in	4.8 in
Product Width	Product Weight
2.1 in	0.7 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag

Performance Ratings

Amperage Rating

50 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW2050](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)