

Eaton QBHW2125

Catalog Number: QBHW2125

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 125A, 22 kAIC, 120/240V , Bolt-on

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW2125 |
| | UPC |
| | 786679382103 |
| Product Length/Depth | Product Height |
| 3.8 in | 4.7 in |
| Product Width | Product Weight |
| 2.3 in | 0.7 lb |
| Warranty | Certifications |
| 1 year | CSA Certified |
| | UL Listed |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag

Performance Ratings

Amperage Rating

125 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW2125](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBHW2125

Catalog Number: QBHW2125

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 125A, 22 kAIC, 120/240V , Bolt-on

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW2125 |
| | UPC |
| | 786679382103 |
| Product Length/Depth | Product Height |
| 3.8 in | 4.7 in |
| Product Width | Product Weight |
| 2.3 in | 0.7 lb |
| Warranty | Certifications |
| 1 year | CSA Certified |
| | UL Listed |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Quicklag

Performance Ratings

Amperage Rating

125 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW2125](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)