

# Eaton QBHW2125

Catalog Number: QBHW2125

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 125A, 22 kAIC, 120/240V , Bolt-on

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB thermal magnetic circuit breaker	QBHW2125
	<b>UPC</b>
	786679382103
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.7 in
<b>Product Width</b>	<b>Product Weight</b>
2.3 in	0.7 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	CSA Certified
	UL Listed
<b>Catalog Notes</b>	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Two-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

125 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

7

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW2125](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)