

# Eaton QBHW3035H

Catalog Number: QBHW3035H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 35 A, 22 kAIC, 240 V, Bolt-on

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB thermal magnetic circuit breaker	QBHW3035H
	UPC
	786679393352
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.7 in
<b>Product Width</b>	<b>Product Weight</b>
3.2 in	1.15 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	CSA Certified
<b>Catalog Notes</b>	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Three-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

35 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

240 V - 240 V

## Miscellaneous

### Quantity

32

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHW3035H](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBHW3035H

Catalog Number: QBHW3035H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 35 A, 22 kAIC, 240 V, Bolt-on

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB thermal magnetic circuit breaker	QBHW3035H
	UPC
	786679393352
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.7 in
<b>Product Width</b>	<b>Product Weight</b>
3.2 in	1.15 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	CSA Certified
<b>Catalog Notes</b>	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Three-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

35 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

240 V - 240 V

## Miscellaneous

### Quantity

32

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHW3035H](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)