

# Eaton QBHW3050H

Catalog Number: QBHW3050H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 50A, 22 kAIC, 240V, Bolt-on



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QB thermal magnetic circuit breaker | QBHW3050H             |
|   | <b>UPC</b>            |
|   | 786679393451          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.8 in                                    | 4.7 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 3.2 in                                    | 1.1 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | CSA Certified         |
|   | UL Listed             |
| <b>Catalog Notes</b>                      |                       |
| HACR rated                                |                       |

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Three-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

240 V - 240 V

## Miscellaneous

### Quantity

32

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW3050H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBHW3050H

Catalog Number: QBHW3050H

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 50A, 22 kAIC, 240V, Bolt-on



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton QB thermal magnetic circuit breaker | QBHW3050H             |
|   | <b>UPC</b>            |
|   | 786679393451          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.8 in                                    | 4.7 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 3.2 in                                    | 1.1 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | CSA Certified         |
|   | UL Listed             |
| <b>Catalog Notes</b>                      |                       |
| HACR rated                                |                       |

## Physical Attributes

### Circuit breaker type

QBHW

### Mounting Method

Bolt-on

### Number of poles

Three-pole

### Type

Quicklag

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

240 V - 240 V

## Miscellaneous

### Quantity

32

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBHW3050H](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)