

Specifications

Eaton QC2015

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 15 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton QC thermal magnetic circuit breaker |
| CATALOG NUMBER | QC2015 |
| UPC | 786679309339 |
| PRODUCT LENGTH/DEPTH | 3.8 in |
| PRODUCT HEIGHT | 4.8 in |
| PRODUCT WIDTH | 2.2 in |
| PRODUCT WEIGHT | 0.65 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL Listed CSA Certified |



Powering Business Worldwide

Physical Attributes

| | |
|-----------------------------|----------------------------|
| CIRCUIT BREAKER TYPE | QC |
| CONNECTION | Cable-in/cable-out |
| NUMBER OF POLES | Two-pole |
| TYPE | Industrial circuit breaker |

Performance Ratings

| | |
|-------------------------|-----------|
| AMPERAGE RATING | 15 A |
| INTERRUPT RATING | 10 kAIC |
| TRIP TYPE | T268 |
| VOLTAGE RATING | 120/240 V |

Miscellaneous

| | |
|----------------|---------------------|
| OPTIONS | Non-interchangeable |
|----------------|---------------------|

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QC2015 |
|--------------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton QC2015

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 15 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable



General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton QC thermal magnetic circuit breaker |
| CATALOG NUMBER | QC2015 |
| UPC | 786679309339 |
| PRODUCT LENGTH/DEPTH | 3.8 in |
| PRODUCT HEIGHT | 4.8 in |
| PRODUCT WIDTH | 2.2 in |
| PRODUCT WEIGHT | 0.65 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | UL Listed CSA Certified |



Powering Business Worldwide

Physical Attributes

| | |
|-----------------------------|----------------------------|
| CIRCUIT BREAKER TYPE | QC |
| CONNECTION | Cable-in/cable-out |
| NUMBER OF POLES | Two-pole |
| TYPE | Industrial circuit breaker |

Performance Ratings

| | |
|-------------------------|-----------|
| AMPERAGE RATING | 15 A |
| INTERRUPT RATING | 10 kAIC |
| TRIP TYPE | T268 |
| VOLTAGE RATING | 120/240 V |

Miscellaneous

| | |
|----------------|---------------------|
| OPTIONS | Non-interchangeable |
|----------------|---------------------|

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QC2015 |
|--------------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

