



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QC3030H Type QC BRKR 3P 30A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC3030H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 30 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.9 In Overall Height, 3.8 In Overall Length
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

### Features

dimensions	3.8000 IN X 3.2000 IN X 4.9000 IN
Poles	3

### Descriptions

Description	TYPE QC BRKR 3P 30A 240VAC MAX 10KAIC
extra long description	ETN QC3030H TYPE QC BREAKER 3P 30A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

### Manufacturer Information

GTIN	00786679240106
UPC	786679240106

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Package	8
Weight Per each	1.1

### Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper ConvergedOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative Energy
standard	UL Listed,CSA Certified