

Specifications



Eaton QCD2060

Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCD, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QCD2060
UPC	786679135969
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.905 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QCD
CONNECTION	Cable-in/cable-out
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Performance Ratings

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QCD2060

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.



Powering Business Worldwide



Eaton QCD2060

Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCD, Non-interchangeable

General specifications

PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QCD2060
UPC	786679135969
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.905 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Physical Attributes

CIRCUIT BREAKER TYPE	QCD
CONNECTION	Cable-in/cable-out
NUMBER OF POLES	Two-pole
TYPE	Industrial circuit breaker

Miscellaneous

OPTIONS	Non-interchangeable
----------------	---------------------

Performance Ratings

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QCD2060

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.