

Specifications



Eaton QCR2030

Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Fixed

General specifications

PRODUCT NAME	Eaton QCR thermal magnetic circuit breaker
CATALOG NUMBER	QCR2030
UPC	786679144343
PRODUCT LENGTH/DEPTH	4.6 in
PRODUCT HEIGHT	1.2 in
PRODUCT WIDTH	3.3 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	1 year
COMPLIANCES	HACR Rated
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Standard breaker terminals are box type lugs.



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QCR
CONNECTION	Cable-in/cable-out
MOUNTING METHOD	Rear
NUMBER OF POLES	Two-pole
TERMINALS	Fixed
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QCR2030
--------------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

