



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QHE2X32T8UNVISLB Ballast

*Sylvania-Ledvance*

Catalog Number	QHE2X32T8UNVISLB
Manufacturer	Sylvania-Ledvance
Description	OBS49838 2 Lamp 32WT8 High Efficiency Instant Start Electronic Ballast, Universal Voltage, Low Ballast Factor Banded 10 PK.
Weight per unit	1.5 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

amperage rating	120
Ballast Factor	0.78
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	2
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10

### Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6810000000000000

### Descriptions

Description	BALLAST
extra long description	SYL QHE-2x32T8/UNV-ISL-SC-B/49838 Q
Long Description	OBS49838 2 lamp 32wT8 High Efficiency Instant Start electronic ballast, universal voltage, low ballast factor banded 10 pk.
Product Type	QHE2X32T8UNVISLSCB 10/CS 1/Sku
Special Features	NO

### Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135498381
Manufacturers Part Number	QHE-2X32T8/UNV-ISL-SC-B/49838
UPC	046135498381

### Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls

### Packaging

Carton	1
Package	10
Weight Per each	1.46