



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ROS250 1/0-250 Awg Direct Burial "Cold Roll-On" Splice

Nsi Industries

| | |
|------------------|---|
| Catalog Number | ROS250 |
| Manufacturer | Nsi Industries |
| Description | Easy-Splice Roll On, Black Insulation Color, Easy Splice Sleeve;Sealant Strip, -40 °C Operating Temperature, +90 °C Operating Temperature, 4.5 In Overall Length, 1000 V, 0.26 LB |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------|-----------------|
| Cable Size | 1/0 AWG-250 MCM |
| Cable Type | Class A-B |
| insulation | EPDM Elastomer |
| Voltage Rating | 1000 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1/0-250 AWG DIRECT BURIAL "COLD ROLL-ON" SPLICE |
| extra long description | NSI ROS-250 Easy-Splice Roll On 250 |
| Special Features | Easy Roll-On Way To Insulate And Seal Cable - Made Of EPDM Elastomer |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381123367 |
| UPC | 662381123367 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | SPLICE KITS |
| Type | Roll-On Splice Kits |

Packaging

| | |
|-----------------|------|
| Carton | 2 |
| Weight Per each | 0.26 |

Uses, Certifications, and Standards

| | |
|--------------------------------|--|
| Application | Splicing Wire |
| Operating Temperature standard | -40 C To 90 C ANSI C119.1-1986 Qualified, UL 486D |