



REDUCING BUSHINGS AND ADAPTERS



R-31



R-65



ADUP-12

Class I, Div. 1 & 2, Groups A,B,C,D
Class I, Zone 1, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G

UL Standard: 1203
 CSA Standard: C22.2 No. 30

LISTED File No. E 10514

Certified File No. LR11716

FEATURES-SPECIFICATIONS

Application

- To reduce the trade size of a taped hole or hub.

Reducer Features

- Tapered threads (NPT)
- Smooth internal bushing protects conductors
- Threaded for Rigid Conduit or IMC

ADUP Features

- Tapered threads (NPT)
- Enlarged drilled and tapped hole openings by an NPT size

Material/Finish

Copper-free Aluminum
 (less than 4/10 of 1%)
 (R-10 through R-109)

Natural Finish

Steel/Zinc Plated
 (RE20S through RE109S)

For ATEX and IEC Ex certified Reducing Bushings and Adapters, contact factory or check the website

Material/Finish

Copper-free Aluminum
 (less than 4/10 of 1%)

Natural Finish

MADE IN THE USA

REDUCING BUSHINGS			
CATALOG NUMBER		HUB SIZE	DIMENSIONS
KILLARK ALUM.	STEEL		BODY LENGTH
R-10	—	1/2" — 3/8"	3/4"(19)
R-20	RE20S	3/4" — 3/8"	11/16"(18)
R-21	RE21S	3/4" — 1/2"	13/16"(21)
R-30	RE30S	1" — 3/8"	11/16"(18)
R-31	RE31S	1" — 1/2"	13/16"(21)
R-32	RE32S	1" — 3/4"	13/16"(21)
R-41	RE41S	1-1/4" — 1/2"	13/16"(21)
R-42	RE42S	1-1/4" — 3/4"	13/16"(21)
R-43	RE43S	1-1/4" — 1"	1"(25)
R-51	RE51S	1-1/2" — 1/2"	13/16"(21)
R-52	RE52S	1-1/2" — 3/4"	13/16"(21)
R-53	RE53S	1-1/2" — 1"	1"(25)
R-54	RE54S	1-1/2" — 1-1/4"	1-1/64"(28)
R-61	RE61S	2" — 1/2"	13/16"(21)
R-62	RE62S	2" — 3/4"	13/16"(21)
R-63	RE63S	2" — 1"	1"(25)
R-64	RE64S	2" — 1-1/4"	1/64"(28)
R-65	RE65S	2" — 1-1/2"	1/32"(31)
R-73	RE73S	2-1/2" — 1"	1"(25)
R-74	RE74S	2-1/2" — 1-1/4"	1" (25)
R-75	RE75S	2-1/2" — 1-1/2"	1"(25)
R-76	RE76S	2-1/2" — 2"	1"(25)
R-84	RE84S	3" — 1-1/4"	1" (25)
R-85	RE85S	3" — 1-1/2"	1-1/4"(32)
R-86	RE86S	3" — 2"	1-1/4"(32)
R-87	RE87S	3" — 2-1/2"	1-1/4"(32)
R-96	RE96S	3-1/2" — 2"	1-3/8"(35)
R-97	RE97S	3-1/2" — 2-1/2"	1-3/8"(35)
R-98	RE98S	3-1/2" — 3"	1-3/8"(35)
R-106	RE106S	4" — 2"	1-1/2"(38)
R-107	RE107S	4" — 2-1/2"	1-1/2"(38)
R-108	RE108S	4" — 3"	1-1/2"(38)
R-109	RE109S	4" — 3-1/2"	1-1/2"(38)

ADUP ADAPTERS		
CATALOG NUMBER	DESCRIPTION	
ADUP-01	Male 3/8"	Female 1/2"
ADUP-12	Male 1/2"	Female 3/4"
ADUP-23	Male 3/4"	Female 1"