



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **R600PI 600W P/DMR SP Iv** *Pass & Seymour/Legrand*

|                  |                               |
|------------------|-------------------------------|
| Catalog Number   | R600PI                        |
| Manufacturer     | Pass & Seymour/Legrand        |
| Description      | Rfi Rotary Dimmer Preset 660W |
| Weight per unit  | 0.0850 (lbs/each)             |
| Product Category | Lighting Dimmers              |

### **Features**

|           |               |
|-----------|---------------|
| Poles     | 1             |
| Wattage   | 600           |
| Wire Size | #14 - #10 Awg |

### **Material, Color, and Finish**

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### **Descriptions**

|                        |                               |
|------------------------|-------------------------------|
| Description            | 600W P/DMR SP IV              |
| extra long description | P&S R600PI DISC SUB R603PIV   |
| Long Description       | RFI Rotary Dimmer Preset 660W |
| Product Type           | Disc Sub R603piv              |

### **Manufacturer Information**

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007045710   |
| Manufacturers Part Number | R600PI           |
| UPC                       | 785007045710     |

### **Taxonomies, Classifications, and Categories**

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Dimmer   |

### **Packaging**

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 24    |
| Weight Per each | 0.085 |

### **Uses, Certifications, and Standards**

|          |           |
|----------|-----------|
| standard | UL, cULus |
|----------|-----------|