



RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: White

Weight: 19.9 lbs

Project:	Type:
Prepared By:	Date:

Lamp Info		Ballast Info	
Type:	T5HO	Type:	Prog. Start
Watts:	324W	120V:	3.00A
Shape/Size:	N/A	208V:	1.77A
Base:	N/A	240V:	1.54A
ANSI:	N/A	277V:	1.33A
Hours:	20,000	Input Watts:	362W
Lamp Lumens:	24,008	Efficiency:	90%
Efficacy:	66 LPW		

Technical Specifications

Listings

UL Listing:

Dry Locations Only. Ceiling Mount Only.

Construction

Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

Reflector:

Aluminum High Performance brilliant bevel segmented reflectors

Base:

Medium Bi Pin

Mounts:

Surface or Chain (Y Hooks included)

Optical

Lamp:

T5HO (not supplied)

Other

CRI:

85

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Electrical

Total Watts:

6x54W

Input Volts:

120-277V

Input Amps:

3.0/1.28.

Ballast Factor:

1.00.

Dimensions



Features

- Qualifies for EPA Act 2005 incentives
- Post-painted, high reflective gloss white powder coat finish
- High Performance, brilliant bevel segmented reflectors
- Easy wiring and maintenance access panel
- Rotary locking lamp holders for vibration security and easy relamping
- Heavy duty 22 gauge steel Rigid strong housing with no sharp edges



RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: White

Weight: 19.9 lbs

Project:	Type:
Prepared By:	Date:

Lamp Info		Ballast Info	
Type:	T5HO	Type:	Prog. Start
Watts:	324W	120V:	3.00A
Shape/Size:	N/A	208V:	1.77A
Base:	N/A	240V:	1.54A
ANSI:	N/A	277V:	1.33A
Hours:	20,000	Input Watts:	362W
Lamp Lumens:	24,008	Efficiency:	90%
Efficacy:	66 LPW		

Technical Specifications

Listings

UL Listing:

Dry Locations Only. Ceiling Mount Only.

Construction

Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

Reflector:

Aluminum High Performance brilliant bevel segmented reflectors

Base:

Medium Bi Pin

Mounts:

Surface or Chain (Y Hooks included)

Optical

Lamp:

T5HO (not supplied)

Other

CRI:

85

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Electrical

Total Watts:

6x54W

Input Volts:

120-277V

Input Amps:

3.0/1.28.

Ballast Factor:

1.00.

Dimensions



Features

- Qualifies for EPA Act 2005 incentives
- Post-painted, high reflective gloss white powder coat finish
- High Performance, brilliant bevel segmented reflectors
- Easy wiring and maintenance access panel
- Rotary locking lamp holders for vibration security and easy relamping
- Heavy duty 22 gauge steel Rigid strong housing with no sharp edges