



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD113I Radiant 3 Switch SP/3-Way + SP + SP Iv *Pass & Seymour/Legrand*

Catalog Number	RCD113I
Manufacturer	Pass & Seymour/Legrand
Description	15A 120V Radiant Combination (2) Single Pole and (1) 3-Way Switches, Ivory
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	120
media	Yes
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Poles	3
Voltage Rating	120

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT 3 SWITCH SP/3-WAY + SP + SP IV
extra long description	P&S RCD113I RADIANT 3 SWITCH, SP/3-
Long Description	15A 120V Radiant Combination (2) Single Pole and (1) 3-Way Switches, Ivory
Product Type	Radiant 3 Switch, SP/3-Way + SP + SP I
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. Unique "Up/Down" switches match the look and feel of radiant paddle switches.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054743
Manufacturers Part Number	RCD113I
UPC	785007054743

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Two Single Pole Switches & Single Pole/3-Way



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.2083

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed