

# Eaton REN-60

Catalog Number: REN-60

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series REN fuse	REN-60
<b>UPC</b>	<b>Product Length/Depth</b>
051712100601	0.82 in
<b>Product Height</b>	<b>Product Width</b>
3 in	3 in
<b>Product Weight</b>	<b>Warranty</b>
1.4 lb	Not Applicable
<b>Compliances</b>	
Not Applicable	

## Electrical rating

### Amperage Rating

60 A

### Interrupt rating

10 kAIC

### Voltage rating

250 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Super lag, time lag, non current-limiting

## Resources

### Catalogs

Bussmann series complete full line catalog no. 1007

REN-60~SUPER LAG RENEWABLE FUSE 60/250

### Multimedia

Bussmann series Fuseology

### Specifications and datasheets

Eaton Specification Sheet - REN-60