

Eaton RF9601WS

Catalog Number: RF9601WS

Eaton Z-Wave plus decorator switch, Power Failure Memory, 15A, 120V, White satin, 60 Hz, LED, CFL, incandescent, MLV, ELV, fluorescent, and halogen, Single-pole, Three-way, Multi-location, Used with RF9517



General specifications

Product Name	Catalog Number
Eaton Z-Wave Plus decorator switch	RF9601WS
UPC	Product Length/Depth
032664755194	1.38 in
Product Height	Product Width
3.81 in	1.8 in
Product Weight	Warranty
0.001 lb	2 year limited
Compliances	Certifications
FCC Compliant	cULus Listed NOM

Product specifications

Special features

Power Failure Memory

Type

Decorator switch

Switch type

Single-pole, multi-location

Load type

FLR

INC

LED

ELV

HAL

CFL

MLV

Frequency rating

60 Hz

Color

White satin

Wiring method

Wire leads

Operating temperature

32 to 104 °F (0 to 40 °C)

Number of ways

Three-way

Voltage rating

120 V

Amperage Rating

15A

Number Of Poles

Single-pole

Resources

Installation instructions

[Z-Wave Plus wireless switch spec sheet](#)

[Z-Wave Plus wireless switch and accessory switch \(RF9601, RF9617\) instruction sheet](#)

Multimedia

[Eaton's new Z-Wave Plus wireless collection](#)

Specifications and datasheets

[Eaton Specification Sheet - RF9601WS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)