



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RF9640NDW Z-Wave Plus Dimmer 300W White

Eaton Wiring Devices

Catalog Number	RF9640NDW
Manufacturer	Eaton Wiring Devices
Description	Eaton Z-Wave Plus Dimmer Switch, White, Single Pole, 120 Vac, 300W Dimmable Led/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer Switch, Multi-Location, 32°F to 104°F (0°C to 40°C) 757242
Weight per unit	0.3700 (lbs/each)
Product Category	Lighting Dimmers

Features

dimensions	1.4200 IN X 1.8000 IN X 4.2000 IN
media	Yes
Voltage Rating	120 V
Wattage	300 W (LED, CFL), 600 W (INC/HAL, ELV, MLV)

Descriptions

Description	Z-WAVE PLUS DIMMER 300W WHITE
extra long description	EWD RF9640-NDW Z-Wave Plus Dimmer 3
Features	Eaton's complete offering of wireless lighting controls are easy to install, require no special wiring and are perfect for both new construction and existing homes. With our Z-Wave Plus wireless collection you get enhanced cybersecurity, improved wireless performance and flexibility to choose from 10 different colors to match your lighting mood and room decor.
Long Description	Eaton Z-Wave plus dimmer switch, White, Single pole, 120 Vac, 300W Dimmable LED/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer switch, Multi-location, 32°F to 104°F (0°C to 40°C) 757242
Product Type	Z-Wave Plus Dimmer 300W White
Special Features	Dimmers

Manufacturer Information

Brand	Eaton
GTIN	00032664757242
Manufacturers Part Number	RF9640-NDW
UPC	032664757242

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 6

Weight Per each 0.37

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other

Operating Temperature 32 to 104 °F (0 to 40 °C)

standard NOM,cULus Listed