

NEER Zinc Offset Nipples and Three Piece Couplings

RN: 3/4" Offset

Applications

- To provide an offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN-50

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Body Length	Maximum Diameter
1/2	RN-50	2.45/62.2	0.94/23.9
3/4	RN-75	2.60/66.0	1.15/29.2
1	RN-100	2.76/70.1	1.40/35.6
1-1/4	RN-125	2.90/73.7	1.84/46.7
1-1/2	RN-150	3.05/77.5	2.06/52.3
2	RN-200	3.23/82.0	2.66/67.6

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish


- Malleable iron/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC-50



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		
		A	B	C
1/2	TPC-50	1.36/34.5	1.30/33.0	1.20/30.5
3/4	TPC-75	1.63/41.4	1.57/39.9	1.30/33.0
1	TPC-100	1.70/43.2	2.13/54.1	1.88/47.8
1-1/4	TPC-125	2.12/53.8	2.44/62.0	2.14/54.4
1-1/2	TPC-150	2.00/50.8	2.89/73.4	2.61/66.3
2	TPC-200	2.38/60.5	3.41/86.6	3.13/79.5
2-1/2	TPC-250	2.54/64.5	4.03/102.4	3.91/99.3
3	TPC-300	2.56/65.0	4.60/116.8	4.36/110.7
3-1/2	TPC-350	2.54/64.5	4.61/117.1	4.37/111.0
4	TPC-400	3.94/100.1	5.61/142.5	5.10/129.5

NEER Zinc Offset Nipples and Three Piece Couplings

RN: 3/4" Offset

Applications

- To provide an offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN-50

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish


- Malleable iron/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC-50



COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS

Commercial Products

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Body Length	Maximum Diameter
1/2	RN-50	2.45/62.2	0.94/23.9
3/4	RN-75	2.60/66.0	1.15/29.2
1	RN-100	2.76/70.1	1.40/35.6
1-1/4	RN-125	2.90/73.7	1.84/46.7
1-1/2	RN-150	3.05/77.5	2.06/52.3
2	RN-200	3.23/82.0	2.66/67.6

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		
		A	B	C
1/2	TPC-50	1.36/34.5	1.30/33.0	1.20/30.5
3/4	TPC-75	1.63/41.4	1.57/39.9	1.30/33.0
1	TPC-100	1.70/43.2	2.13/54.1	1.88/47.8
1-1/4	TPC-125	2.12/53.8	2.44/62.0	2.14/54.4
1-1/2	TPC-150	2.00/50.8	2.89/73.4	2.61/66.3
2	TPC-200	2.38/60.5	3.41/86.6	3.13/79.5
2-1/2	TPC-250	2.54/64.5	4.03/102.4	3.91/99.3
3	TPC-300	2.56/65.0	4.60/116.8	4.36/110.7
3-1/2	TPC-350	2.54/64.5	4.61/117.1	4.37/111.0
4	TPC-400	3.94/100.1	5.61/142.5	5.10/129.5