



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RTTP6030 1-3/8" Tip Bit

L.H. Dottie CO.

Catalog Number	RTTP6030
Manufacturer	L.H. Dottie CO.
Description	Tip Bit, 9 Drill Stages, 5/8 In. Minimum Drill Diameter, 1-3/8 In. Maximum Drill Diameter, M2 High Speed Steel Material, Cobalt Titanium Coated Finish, 1-3/8 In. Size, 1/4 In. Shank Diameter, Hex Shank Type
Weight per unit	0.8000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Material	M2 High Speed Steel
Shank Diameter	1/4
Shank Type	HEX

Material, Color, and Finish

Finish	Cobalt Titanium Coated
--------	------------------------

Dimensions and Weight

Size	1-3/8
------	-------

Descriptions

Description	1-3/8" TIP BIT
extra long description	DOTTIE RTTP6030 1-3/8" Base & 1 Tip
Long Description	Tip Bit, 9 drill stages, 5/8 in. minimum drill diameter, 1-3/8 in. maximum drill diameter, M2 High Speed Steel material, Cobalt Titanium Coated finish, 1-3/8 in. Size, 1/4 in. shank diameter, Hex shank type
Product Type	1-3/8" Base & 1 Tip - Tip Bits
Special Features	Features: Tri-Cut Tip Cuts Smoother, Faster And Cooler, "Plier Tite" Tip Fit

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002812135
Manufacturers Part Number	RTTP6030
UPC	781002812135

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Tip Bit

Packaging

Carton	1
Weight Per each	0.8