

## THREE-GANG SCREWLESS WALL PLATE, BROWN

RWP263 | [radiant](#)

---

### FEATURES & BENEFITS

A step above the standard with no unsightly screws, this modern, low-profile wall plate instantly elevates the look of radiant dimmers, switches, outlets, home automation controls and more.

Available in White, Ivory, Light Almond, Black, Brown and Gray, as well as three metallic finishes: Nickel, Dark Bronze and Antique Brass (all sold separately) to coordinate with most any decor.

- radiant screwless wall plates feature a modern low profile in keeping with today's design trends.
- Molded of rugged .065" thick polycarbonate for greater durability.
- One-piece subplate mounts over the device, allowing you to simply snap on the wall plate with ease.
- Subplate screws align devices to ensure proper positioning of the wall plate.
- An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.
- Opening accommodates all NEMA 26-opening devices.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Special Features: Screwless

#### CONSTRUCTION INFORMATION

Component 4: 78500723185

#### DIMENSIONS

Height (US): 4.94"  
Width (US): 6.77"


#### TECHNICAL INFORMATION

Material: Polycarbonate

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant





## THREE-GANG SCREWLESS WALL PLATE, BROWN

RWP263 | [radiant](#)

---

### FEATURES & BENEFITS

A step above the standard with no unsightly screws, this modern, low-profile wall plate instantly elevates the look of radiant dimmers, switches, outlets, home automation controls and more.

Available in White, Ivory, Light Almond, Black, Brown and Gray, as well as three metallic finishes: Nickel, Dark Bronze and Antique Brass (all sold separately) to coordinate with most any decor.

- radiant screwless wall plates feature a modern low profile in keeping with today's design trends.
- Molded of rugged .065" thick polycarbonate for greater durability.
- One-piece subplate mounts over the device, allowing you to simply snap on the wall plate with ease.
- Subplate screws align devices to ensure proper positioning of the wall plate.
- An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.
- Opening accommodates all NEMA 26-opening devices.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Special Features: Screwless

#### CONSTRUCTION INFORMATION

Component 4: 78500723185

#### DIMENSIONS

Height (US): 4.94"  
Width (US): 6.77"

#### TECHNICAL INFORMATION

Material: Polycarbonate

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

