4.0 Sockets

S10 Socket for 5-pin Relays



10 A / 250 V

Specifications

Rated Load

Rated impulse withstand voltage
- All terminals / DIN rail
- Contact / Terminals
- Contact / Coil terminals
Cross-section of connecting wire
- Single-wire
- Multi-wire
Nominal screw torque
Screw dimensions
Mounting
Ambient temperature operation/storage
Weight

Included Accessories

Retaining Clip, plastic

Optional Accessories

Retaining clip, plastic Bridge bar 5 kV rms / 1 min 2.5 kV rms / 1 min 5 kV rms / 1 min

4 mm²/ AWG 12 or 2 x 2.5 mm²/ AWG 14 0.34mm²/ 22 - 2.5 mm²/ AWG 14 0.7 Nm M3 Pozi slot TS-35 or Back Panel Mounting -40....60 °C /-40 ... 80 °C (no ice) 23g

S10-C for C10 / C10x Relays


S10-C / CP-17B (BAG 10 PCS) for C10 / C10x S10-BB (BAG 20 PCS)



Ξ

rurc

Connection diagram



Dimensions [mm]

