



# S1906

F13T5/CW  
13 watt; T5; Preheat Fluorescent; 4200K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1906

| Item Number | UPC          | Watts | Lamp Shape | Base             | ANSI Base | Lamp Code | MOD In Inches |
|-------------|--------------|-------|------------|------------------|-----------|-----------|---------------|
| S1906       | 045923019067 | 13    | T5         | Miniature Bi Pin | G5        | F13T5/CW  | 0.63"         |

| MOL In Inches | Nominal Length | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack   | CRI |
|---------------|----------------|----------------|---------------------|-------------|------------|--------|-----|
| 20.91"        | 21"            | 860            | 5000                | 4200        | Cool White | 200/10 | 62  |

| RoHS Compliant |
|----------------|
| Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S1906

F13T5/CW  
13 watt; T5; Preheat Fluorescent; 4200K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1906

| Item Number | UPC          | Watts | Lamp Shape | Base             | ANSI Base | Lamp Code | MOD In Inches |
|-------------|--------------|-------|------------|------------------|-----------|-----------|---------------|
| S1906       | 045923019067 | 13    | T5         | Miniature Bi Pin | G5        | F13T5/CW  | 0.63"         |

| MOL In Inches | Nominal Length | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack   | CRI |
|---------------|----------------|----------------|---------------------|-------------|------------|--------|-----|
| 20.91"        | 21"            | 860            | 5000                | 4200        | Cool White | 200/10 | 62  |

| RoHS Compliant |
|----------------|
| Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

