



# S1906

F13T5/CW  
13 watt; T5; Preheat Fluorescent; 4200K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1906

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S1906	045923019067	13	T5	Miniature Bi Pin	G5	F13T5/CW	0.63"

MOL In Inches	Nominal Length	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	CRI
20.91"	21"	860	5000	4200	Cool White	200/10	62

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S1906

F13T5/CW  
13 watt; T5; Preheat Fluorescent; 4200K Cool White; 62 CRI;  
Miniature Bi Pin base

### Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S1906

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S1906	045923019067	13	T5	Miniature Bi Pin	G5	F13T5/CW	0.63"

MOL In Inches	Nominal Length	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	CRI
20.91"	21"	860	5000	4200	Cool White	200/10	62

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

