



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S202D10 MCB 2P D 10A 480Y/277 Supp

Industrial Connections &

Catalog Number	S202D10
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, Supplementary Protector, Rated Current 10 Amps, 2 Pole, Interrupt Rating 6 Ka, Thermal Magnetic Trip Curve D, Voltage Up to 277/Y480 Vac, 60/110 VDC, Din Rail Mounted, Finger Safe and Multi-Function Terminals, UI 1077, Csa 22.2 No. 235
Weight per unit	0.5600 (lbs/each)
Product Category	2 Pole Supplementary Protector

Features

amperage rating	10 in
interrupt rating	6 kA
Poles	2 in
Trip Type	RIGHT ANGLE FITTING, RIGHT ANGLE FITTING TYPE; ABS PLASTIC MATERIAL; 2 INCH L X 2 INCH W X 0.58 INCH H SIZE; WHITE FINISH; PAN-WAY LD5 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 20 STANDARD PACKAGE; PAN-WAY[R] BRAND; ROHS COMPLIANT
Voltage Rating	480Y/277V AC

Dimensions and Weight

Height	88 Millimeters
Length	69 Millimeters
Width	35 W

Descriptions

Description	MCB 2P D 10A 480Y/277 SUPP
extra long description	ABB S202-D10 LEGACY SEE REPLACEMENT
Long Description	Miniature Circuit Breaker, Supplementary Protector, Rated Current 10 Amps, 2 Pole, Interrupt Rating 6 kA, Thermal Magnetic Trip Curve D, Voltage up to 277/Y480 VAC, 60/110 VDC, DIN Rail Mounted, Finger Safe and Multi-Function Terminals, UL 1077, CSA 22.2 No. 235
Product Type	Legacy See Replacement MCB 2P D 10a
Special Features	High performance MCB provides compact supplementary, energy limiting, circuit protection



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	ABB
GTIN	00662019170800
Manufacturers Part Number	S202-D10
UPC	662019170800

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Miniature circuit breakers

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	5
Weight Per each	0.56

Uses, Certifications, and Standards

Application	For use as a supplemental protection device
Frequency Rating	50/60 Hz
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL mA