



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S203UK25 MCB 3P K 25A 240 Vac

Industrial Connections &

Catalog Number	S203UK25
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, Branch Circuit Protection, Rated Current 25 Amps, 3 Pole, Interrupt Rating 10 Ka, Thermal Magnetic Trip Curve K, Voltage Up to 240 Vac, Din Rail Mounted, Finger Safe and Multi-Function Terminals, UI 489, Csa 22.2 No. 5
Weight per unit	0.9200 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

amperage rating	25 W
interrupt rating	10 kA
Poles	3 WTT
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND
Voltage Rating	240 W

Dimensions and Weight

Height	92mm
Length	71 Millimeters
Width	52.5mm

Descriptions

Description	MCB 3P K 25A 240 VAC
extra long description	ABB S203U-K25 MCB 3P K 0.5A 240 BCP
Long Description	Miniature Circuit Breaker, Branch Circuit Protection, Rated Current 25 Amps, 3 Pole, Interrupt Rating 10 kA, Thermal Magnetic Trip Curve K, Voltage up to 240 VAC, DIN Rail Mounted, Finger Safe and Multi-Function Terminals, UL 489, CSA 22.2 No. 5
Product Type	MCB S200U 3P 25A CRB K 240VCA BCCB
Special Features	DIN Rail Mounting, Finger Safe and Multi-Function Terminals

Manufacturer Information

Brand	ABB
GTIN	00662019170497
Manufacturers Part Number	S203U-K25
UPC	662019170497



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	High Performance MCB, Branch Circuit Protection

Packaging

Carton	1
Package	3
Weight Per each	0.92

Uses, Certifications, and Standards

Application	For use as branch protection
Frequency Rating	50/60 Hz
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL 489, CSA 22.2 No. 5, IEC 60947-2, UL E212323