



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S26565 20W T12 24" 41K Med Bi-Pin Base 62 Cri 1200LM

Satco

Catalog Number	S26565
Manufacturer	Satco
Description	20 Watt - Fluorescent T12 - 4100K - Medium Bi-Pin (G13) Base
Weight per unit	0.3700 (lbs/each)
Product Category	Lighting

Features

average life	10000
Base	Medium Bi Pin
beam angle	360
lumens	1.2k
Shape	T12

Material, Color, and Finish

color temperature	4100
Finish	white

Dimensions and Weight

Diameter	1.5
Length	23.22

Descriptions

Description	20W T12 24" 41K MED BI-PIN BASE 62 CRI 1200LM
extra long description	SATCO S26565 F20T12/CW
Long Description	20 Watt - Fluorescent T12 - 4100K - Medium Bi-pin (G13) Base
Product Type	F20T12/CW
Special Features	Lawful for sale in California ; Warranty: Average Rated Hour Limited ; Indoor use ; Operating Temperature: Ballast Dependent ; MOQ: 30 ; RoHS Compliant: No ; Operating Frequency: 50/60 Hz ; Material: Glass

Manufacturer Information

Brand	Satco
GTIN	00045923265655
Manufacturers Part Number	S26565
UPC	045923265655

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	T12 Linear



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	30
Weight	0.0049
Weight Per each	0.37

Uses, Certifications, and Standards

standard	Unlisted
----------	----------