



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29589 9.5A19/Led/30K/ND/120V/4P Satco

Catalog Number	S29589
Manufacturer	Satco
Description	9.5W A19 Led Lamp Frosted 30K E26 220' Beam 120V Non-Dimmable 4-PK
Weight per unit	0.5800 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	15000
Base	Medium
beam angle	220
dimnable	No
lumens	800
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

color temperature	3000
-------------------	------

Dimensions and Weight

Diameter	2.38
Length	4.38

Descriptions

Description	9.5A19/LED/30K/ND/120V/4P
extra long description	SATCO S29589 9.5A19/LED/30K/ND/120V
Long Description	9.5W A19 LED Lamp Frosted 30K E26 220' Beam 120V Non-Dimmable 4-PK
Product Type	9.5A19/Led/30K/ND/120V/4PK
Special Features	Enclosed fixture rated: Yes ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Energy Star rated: Yes ; Lamp appearance: Frosted White ; Incandescent equivalent: 60 watts

Manufacturer Information

Brand	Satco
GTIN	00045923295898
Manufacturers Part Number	S29589
UPC	045923295898



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type Type A

Packaging

Carton 1

Weight Per each 0.58

Uses, Certifications, and Standards

Operating Temperature -25C (-13F) to a maximum of +45C (+113F)