

Project Name

Location

Prepared By



SATCO S29812

11A19/LED/4000K/1100L/120V/D

Notes

[www] 01-15-2024 02:40:10

General

Status	Active
Watts	11W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	80
Lumens	1100L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.79
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	4.331
MOD	2.362
Weight (lb.)	0.07

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307673
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S8483
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Washington Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp



Project Name

Location

Prepared By



SATCO S29812

11A19/LED/4000K/1100L/120V/D

Notes

[www] 01-15-2024 02:40:10

General

Status	Active
Watts	11W
Incandescent Equivalent	75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	80
Lumens	1100L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.79
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	4.331
MOD	2.362
Weight (lb.)	0.07

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307673
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S8483
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Washington Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

