

Project Name

Location

Prepared By

**SATCO S29825**

7A19/SW/LED/E26/27K/120V

Notes

(www) 05-28-2023 00:27:09

General

Status	Discontinued
Substitute	S12419
Watts	7W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Soft White
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	80+
Lumens	800L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	15000
Product Category	Type A
Technology	LED

Electrical

Operating Temperature	-20C (-4F) to +45C (+113F)
-----------------------	----------------------------

Physical

MOL	4.13
MOD	2.38

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	2-Years

Compliance

Safety Listing	cULus
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp