

S29837 A19 LED

9.8A19/OMNI/220/LED/35K

| | |
|---------------------------|----------------|
| Lamp Type | LED |
| Bulb Type | A19 |
| Base Type | E26 |
| Wattage | 9.8 |
| Color Temperature | 3500 |
| Color Rendering Index CRI | 80 |
| Warranty | 3 Year Limited |



Lighting Facts Per Bulb

| | |
|---|-------------------|
| Brightness | 800 lumens |
| Estimated Energy Cost | \$1.08 |
| per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use. | |
| Average Life | 22.8 years |
| Based on 3 hrs/day | |
| Light Appearance | |
| | |
| Energy Used | 9 watts |

Product Specifications

| Item Number | Technology | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base |
|-------------|-------------------------|-----------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| S29837 | LED | *20045923298374 | 120 | 9.8 | 60 | A19 | Medium |
| ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL in inches | MOD in inches | Initial Lumens | Average Rated Hours |
| E26 | 9.8A19/OMNI/220/LED/35K | Yes | n/a | 4 3/16 | 2 3/8 | 800 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant |
| 3500 | Neutral White | 80 | 220 | 24 | Box | Yes | Yes |

S29837 A19 LED

9.8A19/OMNI/220/LED/35K

| | |
|---------------------------|----------------|
| Lamp Type | LED |
| Bulb Type | A19 |
| Base Type | E26 |
| Wattage | 9.8 |
| Color Temperature | 3500 |
| Color Rendering Index CRI | 80 |
| Warranty | 3 Year Limited |



Lighting Facts Per Bulb

| | |
|---|-------------------|
| Brightness | 800 lumens |
| Estimated Energy Cost | \$1.08 |
| per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use. | |
| Average Life | 22.8 years |
| Based on 3 hrs/day | |
| Light Appearance | |
| | |
| Energy Used | 9 watts |

Product Specifications

| Item Number | Technology | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base |
|-------------|-------------------------|-----------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| S29837 | LED | *20045923298374 | 120 | 9.8 | 60 | A19 | Medium |
| ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL in inches | MOD in inches | Initial Lumens | Average Rated Hours |
| E26 | 9.8A19/OMNI/220/LED/35K | Yes | n/a | 4 3/16 | 2 3/8 | 800 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant |
| 3500 | Neutral White | 80 | 220 | 24 | Box | Yes | Yes |