

Project Name

Location

Prepared By



SATCO S29839

9.8A19/OMNI/220/LED/50K

Notes

[www] 02-16-2023 11:20:04

General

| | |
|-------------------------|---------------|
| Status | Active |
| Watts | 9.8W |
| Incandescent Equivalent | 60W |
| Volts | 120V |
| Shape | A19 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Frost |
| CCT (Kelvin) | 5000K |
| Temperature | Natural Light |
| CRI | 80+ |
| Lumens | 800L |
| Beam Spread | 220 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 25000 |
| Product Category | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|-----------------------------|
| Operating Frequency | 60Hz |
| Power Factor | 0.98 |
| Operating Temperature | -25C (-13F) to +45C (+113F) |

Physical

| | |
|--------------|-------|
| MOL | 4.331 |
| MOD | 2.362 |
| Weight (lb.) | 0.06 |

Additional Information

| | |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 5 Year Limited - 10 hr per day |

Compliance

| | |
|---------------------------------|-----------------------------------|
| Safety Listing | cULus - Certified; cULus - Listed |
| Location Rating | Damp |
| California Status | Non-Compliant |
| Title 20 / 24 Status | Non-Compliant |
| California Compliant Substitute | S8481 |
| Colorado Status | Lawful for sale |
| Hawaii Status | Lawful for sale |
| Nevada Status | Lawful for sale |
| Vermont Status | Lawful for sale |
| Washington Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |