



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29839 9.8W Led A19 50K 800LM Dim Satco

Catalog Number	S29839
Manufacturer	Satco
Description	9.8 Watt - A19 Led - 5000K - Medium Base - 220' Beam Spread - 120 Volts
Weight per unit	0.1900 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	25000
connection	Medium
Fixture Type	Type A
lumens	800
Material	Metal;Plastic
Shape	A19
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

Color	Frosted White
-------	---------------

Dimensions and Weight

Size	MOL: 4.19, MOD: 2.38
------	----------------------

Descriptions

Description	9.8W LED A19 50K 800LM DIM
extra long description	SATCO S29839 9.8A19/OMNI/220/LED/50
Long Description	9.8 Watt - A19 LED - 5000K - Medium Base - 220' Beam Spread - 120 Volts
Product Type	9.8A19/Omni/220/Led/50K
Special Features	Dimmable: Yes Dimmable;Operating Temp: -20C (-4F) to a maximum of +45C (+113F);Power Factor: 0.98;Safety Listing: cULus - Damp;SDS Class: LED_Lamp;Tested Lumens: 800

Manufacturer Information

Brand	Satco
GTIN	00045923298394
Manufacturers Part Number	S29839
UPC	045923298394

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.19

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cULus - Damp