

Project Name

Location

Prepared By



# SATCO S29879

8A19/CL/LED/E26/27K/90CRI

**Notes**

(www) 02-24-2023 09:53:31

**General**

Status	Discontinued
Substitute	S39879
Watts	8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90+
Lumens	800L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Product Category	Type A
Technology	LED

**Electrical**

Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

**Physical**

MOL	4.13
MOD	2.38

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Project Name

Location

Prepared By



## SATCO S29879

8A19/CL/LED/E26/27K/90CRI

**Notes**

(www) 02-24-2023 09:53:31

**General**

Status	Discontinued
Substitute	S39879
Watts	8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	90+
Lumens	800L
Beam Spread	360
Dimmable	Yes-Dimmable
Hours Rated	15000
Product Category	Type A
Technology	LED

**Electrical**

Power Factor	0.9
Operating Temperature	-20C (-4F) to +45C (+113F)

**Physical**

MOL	4.13
MOD	2.38

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp