



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S29918 40W Led T8 96" 40K DBL End Wiring SNGL Pin 5500LM

Satco

Catalog Number	S29918
Manufacturer	Satco
Description	40W 8 FT. T8 Led FA8 Base - 40K 50K Average Rated Hours 5500L Type B BBP Double End Wiring DLC 5.1
Weight per unit	0.8800 (lbs/each)
Product Category	Lighting

Features

Base	Single Pin
beam angle	210
lumens	5.5k
Material	Glass
Shape	T8
Warranty	5 Year Limited - T8 LED Bulbs

Material, Color, and Finish

color temperature	4000
Finish	white

Dimensions and Weight

Size	94
------	----

Descriptions

Description	40W LED T8 96" 40K DBL END WIRING SNGL PIN 5500LM
extra long description	SATCO S29918 40T8/LED/96-840/BP/FA8
Long Description	40W 8 ft. T8 LED FA8 Base - 40K 50K Average Rated Hours 5500L Type B BBP Double End Wiring DLC 5.1
Product Type	40T8/Led/96-840/BP/Fa8
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - T8 LED Bulbs ; Fluorescent Equivalent: 59W ; DLC Approved: Yes ; Dimmable: Non-Dimmable ; Additional Information: Suitable for Emergency Lighting only with Satco EM Driver #S8002 ; Material: Glass ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) ; Shatterproof: Yes ; Location Rating: Damp

Manufacturer Information

Brand	Satco
GTIN	00045923299186
Manufacturers Part Number	S29918
UPC	045923299186



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	T8

Packaging

Carton	10
Weight	0.88
Weight Per each	0.88

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus