



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299

## S29919 40W Led T8 96" 50K DBL Ended Wiring 5500LM

Satco

|                  |   |
|------------------|---|
| Catalog Number   | S29919  |
| Manufacturer     | Satco   |
| Description      | 40W 8 FT. T8 Led FA8 Base - 50K 50K Average Rated Hours 5500L<br>Type B BBP Double End Wiring DLC 5.1 |
| Weight per unit  | 1.4 (lbs/each)  |
| Product Category | Lighting  |

### Features

|                |                               |
|----------------|-------------------------------|
| average life   | 50000                         |
| Base           | Fa8                           |
| beam angle     | 210                           |
| lumens         | 5500                          |
| Material       | Glass                         |
| Power Factor   | 0.9                           |
| Shape          | T8                            |
| Voltage Rating | 120 to 277                    |
| Warranty       | 5 Year Limited - T8 LED Bulbs |
| Wattage        | 40                            |

### Material, Color, and Finish

|                             |       |
|-----------------------------|-------|
| color rendering index (cri) | 80+   |
| color temperature           | 5000  |
| Finish                      | white |

### Dimensions and Weight

|      |    |
|------|----|
| Size | 94 |
|------|----|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 40W LED T8 96" 50K DBL ENDED WIRING 5500LM  |
| extra long description | SATCO S29919 40T8/LED/96-850/BP/FA8   |
| Long Description       | 40W 8 ft. T8 LED FA8 Base - 50K 50K Average Rated Hours 5500L<br>Type B BBP Double End Wiring DLC 5.1   |
| Product Type           | 40T8/Led/96-850/BP/FA8  |
| Special Features       | Warranty: 5-Years ; Location Rating: Damp ; Operating Temp:<br>-20C (-4F) to +45C (+113F) ; Material: Glass ; Indoor Outdoor:<br>Indoor ; Color Temp: Natural Light ; Efficacy: 137.50 LPW ; DLC<br>Approved: True ; FCC Compliant: True ; NSF Approved: Yes ;<br>Indoor Outdoor: Indoor ; Lamp Filament: LED ; ANSI Base: Fa8 ;<br>Lamp Ballast Type AB: Type B ; Amps: 0.333-0.144A ; T24<br>Compliant: False |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Satco          |
| GTIN                      | 00045923299193 |
| Manufacturers Part Number | S29919         |
| UPC                       | 045923299193   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type                 | LED Linear   |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Weight          | 0.88 |
| Weight Per each | 1.37 |

## Uses, Certifications, and Standards

|                                |  |
|--------------------------------|--|
| Application                    | LED  |
| Operating Temperature standard | -20C (-4F) to a maximum of +45C (+113F)<br>cRUus - Recognized Component;cULus - Certified;cULus - Classified |