

## Motion Sensors



Catalog #	Wt.
<b>SO</b>	Sensor only, 1500 watt INC capacity, 120V bronze .7 lbs
<b>SO-W</b>	Sensor only, 1500 watt INC capacity, 120V white .7 lbs
<b>S2LH</b>	Sensor, twin 150 watt lampholders, coverplate, bronze 1.7 lbs
<b>S2LH-W</b>	Sensor, twin 150 watt lampholders, coverplate, white 1.7 lbs
<b>MO</b>	Sensor only, 500 watt INC capacity, 120V bronze .5 lbs
<b>MO-W</b>	Sensor only, 500 watt INC capacity, 120V white .5 lbs
<b>M2LH</b>	Sensor, twin 150 watt lampholders, coverplate, bronze 1.2 lbs
<b>M2LH-W</b>	Sensor, twin 150 watt lampholders, coverplate, white 1.2 lbs
<b>R2LHQ</b>	Sensor, twin 75 watt quartz decorative lampholders and coverplate, bronze, lamps included 1.5 lbs
<b>R2LHQ-W</b>	Sensor, twin 75 watt quartz decorative lampholders and coverplate, white, lamps included 1.5 lbs

**Description**  
 Motion Sensors for security and welcome lighting. S Series units have wide 270° field and kits have aluminum lampholders and cover. Center focal range is 50-75 feet. M Series has 130° detection field, 40 foot center range and non-metallic lampholders and cover. Sensor has 1/2" knuckle mount, adjustable time on and sensitivity controls. Bronze or white finish. UL listed for wet locations.

Quartz motion sensors. Attractive security floodlight set. Powerful 75 watt G8 quartz floods controlled by 130° motion sensor so you save energy – lights only when you need it!



# WALKWAY & PATH

## Louverlights



Catalog #	Wt.
<b>587M-VG</b>	Two Tier, 60 watt max. 120V, verdi 2.75 lbs
<b>583M-VG</b>	Three Tier, 100 watt max. 120V, verdi 3.25 lbs
<b>GP12BL</b>	Ground post with stabilizers, non-metallic, black 2.50 lbs

**Description**  
 Louverlights illuminate and accent walkways, driveways and flower beds. Metal construction, verdi finish, frosted glass globes for source brightness reduction, 1/2" hub, UL wet location listed.



# LAMP HOLDERS

## Lampholders



Catalog #	Wt.
<b>101-B</b>	Unshielded, 150 watt max., 120V bronze 0.5 lbs
<b>103-7</b>	Shielded, 150 watt max., 120V bronze 1.25 lbs
<b>103-74</b>	Shielded, 150 watt max., 120V white 1.25 lbs
<b>309-M51-ML</b>	Deep shielded, 150 watt max., 120V bronze 3 lbs
<b>309-M54-ML</b>	Deep shielded, 150 watt max., 120V white 3 lbs

**Description**  
 Cast aluminum units with protective powder paint finish. A variety of unshielded, shielded, and deeply shielded designs for various application requirements. 1/2" cast aluminum swivel knuckle mounting. For use in wet locations. Universal aiming capability. Use PAR lamps outdoors (309 Series can use PAR or BR lamps outdoors).



## Motion Sensors



Catalog #	Wt.	Description
<b>SO</b>	1500 watt INC capacity, 120V bronze .7 lbs	Motion Sensors for security and welcome lighting.
<b>SO-W</b>	1500 watt INC capacity, 120V white .7 lbs	S Series units have wide 270° field and kits have aluminum lampholders and cover. Center focal range is 50-75 feet.
<b>S2LH</b>	Sensor, twin 150 watt lampholders, coverplate, bronze 1.7 lbs	M Series has 130° detection field, 40 foot center range and non-metallic lampholders and cover. Sensor has 1/2" knuckle mount, adjustable time on and sensitivity controls. Bronze or white finish. UL listed for wet locations.
<b>S2LH-W</b>	Sensor, twin 150 watt lampholders, coverplate, white 1.7 lbs	
<b>MO</b>	Sensor only, 500 watt INC capacity, 120V bronze .5 lbs	
<b>MO-W</b>	Sensor only, 500 watt INC capacity, 120V white .5 lbs	
<b>M2LH</b>	Sensor, twin 150 watt lampholders, coverplate, bronze 1.2 lbs	
<b>M2LH-W</b>	Sensor, twin 150 watt lampholders, coverplate, white 1.2 lbs	
<b>R2LHQ</b>	Sensor, twin 75 watt quartz decorative lampholders and coverplate, bronze, lamps included 1.5 lbs	Quartz motion sensors. Attractive security floodlight set. Powerful 75 watt G8 quartz floods controlled by 130° motion sensor so you save energy – lights only when you need it!
<b>R2LHQ-W</b>	Sensor, twin 75 watt quartz decorative lampholders and coverplate, white, lamps included 1.5 lbs	



# WALKWAY & PATH

## Louverlights



Catalog #	Wt.	Description
<b>587M-VG</b>	Two Tier, 60 watt max. 120V, verdi 2.75 lbs	Louverlights illuminate and accent walkways, driveways and flower beds. Metal construction, verdi finish, frosted glass globes for source brightness reduction, 1/2" hub, UL wet location listed.
<b>583M-VG</b>	Three Tier, 100 watt max. 120V, verdi 3.25 lbs	
<b>GP12BL</b>	Ground post with stabilizers, non-metallic, black 2.50 lbs	Ground post, PVC construction with 4 stabilizers and cap.



# LAMP HOLDERS

## Lampholders



Catalog #	Wt.	Description
<b>101-B</b>	Unshielded, 150 watt max., 120V bronze 0.5 lbs	Cast aluminum units with protective powder paint finish. A variety of unshielded, shielded, and deeply shielded designs for various application requirements. 1/2" cast aluminum swivel knuckle mounting. For use in wet locations. Universal aiming capability. Use PAR lamps outdoors (309 Series can use PAR or BR lamps outdoors).
<b>103-7</b>	Shielded, 150 watt max., 120V bronze 1.25 lbs	
<b>103-74</b>	Shielded, 150 watt max., 120V white 1.25 lbs	
<b>309-M51-ML</b>	Deep shielded, 150 watt max., 120V bronze 3 lbs	
<b>309-M54-ML</b>	Deep shielded, 150 watt max., 120V white 3 lbs	

